

# XF2M Rotary Backlock connector (0.5mm-pitch, Dual-sided Contact)


## Rotary Backlock Connectors Provide High-reliability and Superior Work Efficiency. For FPC/FFC

Dual-sided contact reduces the number of parts.

Applicable FPC/FFC thickness of 0.3 mm (Gold-plated type).

Halogen Free (\*)

\* OMRON uses the following standard to determine halogen-free construction: 900 ppm max. for Br, 900 ppm max. for Cl, and 1,500 ppm max. for Br+Cl.



Image

3D

[Contact us](#)

[FAQ](#)

RoHS Compliant

Korean

[Datasheet](#)

Chinese

[目录](#)

English

[Datasheet](#)

English

[FPC/FFC Connectors XF Series](#)

English

[Connector Selection](#)

**Note:** This web page provides an excerpt from a datasheet. Refer to Product Datasheet and other applicable documents for more information.

100pcs per reel

Pins *1	Model	Pins *1	Model	Pins *1	Model	Quantity per reel (unit) *2
6	XF2M-0615-1A-R100	24	XF2M-2415-1A-R100	38	XF2M-3815-1A-R100	100
8	XF2M-0815-1A-R100	26	XF2M-2615-1A-R100	40	XF2M-4015-1A-R100	
10	XF2M-1015-1A-R100	30	XF2M-3015-1A-R100	42	XF2M-4215-1A-R100	
12	XF2M-1215-1A-R100	32	XF2M-3215-1A-R100	45	XF2M-4515-1A-R100	
14	XF2M-1415-1A-R100	33	XF2M-3315-1A-R100	50	XF2M-5015-1A-R100	
18	XF2M-1815-1A-R100	34	XF2M-3415-1A-R100	54	XF2M-5415-1AH-R100	
20	XF2M-2015-1A-R100	35	XF2M-3515-1A-R100	55	XF2M-5515-1AH-R100	
22	XF2M-2215-1A-R100	36	XF2M-3615-1A-R100	60	XF2M-6015-1AH-R100	

\*1 Please consult your OMRON representative for available pin count.

\*2 Please order by integer multiple of the quantity per reel.

1500pcs per reel

Pins *1	Model	Pins *1	Model	Pins *1	Model	Quantity per reel (unit) *2
6	XF2M-0615-1A	24	XF2M-2415-1A	38	XF2M-3815-1A	1,500
8	XF2M-0815-1A	26	XF2M-2615-1A	40	XF2M-4015-1A	
10	XF2M-1015-1A	30	XF2M-3015-1A	42	XF2M-4215-1A	
12	XF2M-1215-1A	32	XF2M-3215-1A	45	XF2M-4515-1A	
14	XF2M-1415-1A	33	XF2M-3315-1A	50	XF2M-5015-1A	
18	XF2M-1815-1A	34	XF2M-3415-1A	54	XF2M-5415-1AH	
20	XF2M-2015-1A	35	XF2M-3515-1A	55	XF2M-5515-1AH	
22	XF2M-2215-1A	36	XF2M-3615-1A	60	XF2M-6015-1AH	

\*1 Please consult your OMRON representative for available pin count.

\*2 Please consult your OMRON representative for available pin count and release date of pin count with bracket.

